PRODUCED BY AN AUTODESK EDUCATIONAL PRODUCT NOTES: 1. MATERIAL: 2. MAXIMUM ROUGHNESS ¹²⁵✓ UNLESS SPECIFIED. 3. REMOVE ALL BURRS AND SHARP EDGES UNLESS SPECIFIED. sample tray -Window center lens mount-place for the ferrulelens hole 7mm (lens Ø6mm) **PRODUCED BY** mirror mount SECTION A-A .394 (1Ómm) SCALE 6: 1 PART MODEL FILENAME **GENERAL** NATIONAL HIGH MAGNETIC FIELD LABORATORY 3605-0101-0003 holder.ipt **TOLERANCES** 1800 E PAUL DIRAC DRIVE MODELED 1 PL DEC: ± 0.020 TALLAHASSEE, FLORIDA 32310 7/25/2012 semenov 2 PL DEC: ± 0.010 DETAILED 7/25/2012 NATIONAL HIGH MAGNETIC FIELD LAB semenov 3 PL DEC: ± 0.005 CHECKED This drawing and the information it contains are both property of the THIRD ANGLE PROJECTION ANGLES: $\pm 1^{\circ}$ Florida State University and are to be held by the recipient as confidential and are not to be transferred to any third party, used to UNLESS OTHERWISE make or furnish information for making any physical structure or any 3605-0101-0003 holder SPECIFIED, DIMENSIONS pictorial, graphic or verbal representation of any information ARE IN INCHES. DO NOT contained herein or copied (unless supplied in productive form) SCALE DRAWING without the express written consent of the Florida State University. SHT 1 OF 1